








<b>A</b>	Skin	Size	
		28" x 28"	W H
	1x1 Flat Front	1x1 Flat Front Shown as it will appear on the Xpressions unit	
<b>B</b>	Skin	Size	
		28" x 28"	W H
	1x1 Flat Front	1x1 Flat Front Shown as it will appear on the Xpressions unit	
<b>C</b>	Skin	Size	
		28" x 28"	W H
	1x1 Flat Front	1x1 Flat Front Shown as it will appear on the Xpressions unit	
<b>D</b>	Skin	Size	
		59" x 28"	W H
	2X1 Horizontal Thread	2X1 Thread Horizontal Shown as it will appear on the Xpressions unit	
<b>E</b>	Skin	Size	
		59" x 28"	W H
	2X1 Horizontal Thread	2X1 Thread Horizontal Shown as it will appear on the Xpressions unit	
<b>F</b>	Skin	Size	
		59" x 28"	W H
	2X1 Horizontal Thread	2X1 Thread Horizontal Shown as it will appear on the Xpressions unit	



**Focus Area Key**  
focus area is always 3"-5" inside edge of all four sides on all skin styles and sizes