







G	Skin	Size	
	28"	28"	W
		x	H
		28"	
		1x1 Flat Back Shown as it will appear on the Xpressions unit	
1x1 Flat Back			


A	Skin	Size	
	28"	28"	W
		x	H
		28"	
		1x1 Flat Front Shown as it will appear on the Xpressions unit	
1x1 Flat Front			


B	Skin	Size	
	28.5"	28.5"	W
		x	H
		28.5"	
		1x1 Single Twist Shown as it will appear on the Xpressions unit	
1x1 Single Twist			

C	Skin	Size	
	28.5"	28.5"	W
		x	H
		28.5"	
1x1 Single Twist		1x1 Single Twist Shown as it will appear on the Xpressions unit	

D	Skin	Size		
	28.5"	28.5"	W	
		x	H	
		28.5"		
		1x1 Single Twist		1x1 Single Twist Shown as it will appear on the Xpressions unit

E	Skin	Size	
	28.5"	28.5"	W
		x	H
		28.5"	
		1x1 Single Twist Shown as it will appear on the Xpressions unit	
1x1 Single Twist			

F	Skin	Size	
	28.5"	28.5"	W
		x	H
		28.5"	
		1x1 Single Twist Shown as it will appear on the Xpressions unit	
1x1 Single Twist			



Focus Area Key
focus area is always 3"-5" inside edge of all four sides on all skin styles and sizes